



**1**

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h	k
M 2	9	4,5	5,3	2
M 2,5	11	5	6,5	2,5
M 3	12	6	7,5	2,5
M 4	16	8	9,5	3,5
M 5	20	10	11,5	4
M 6	24	12	15	5
M 8	30	16	18	6
M 10	36	20	23	8
M 12	40	22	25	10

**Specification**

- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened **—**
  - Zinc plated, blue passivated **ZB**
- Stainless steel AISI 303 **NI**  
Matte shot-blasted
- *Strength Values of Nuts* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**2**

**Information**

Flat knurled nuts DIN 466 are suitable for universal use and can be tightened and loosened easily without tools. A nut with thread M12 is also available in addition to the types defined in the DIN standard.

see also...

- *Stainless Steel Knurled Nuts GN 536* → Page 640
- *Stainless Steel Knurled Nuts DIN 6303* → Page 643
- *Knurled Nuts DIN 466 with Loss Protection GN 111.7* → Page 2084
- *Knurled Nuts DIN 467* → Page 648

How to order (Steel, blackened)	1	d <sub>1</sub>
<b>DIN 466-M6</b>		
How to order (Steel, zinc plated)	1	d <sub>1</sub>
<b>DIN 466-M10-ZB</b>	2	Finish
How to order (Stainless steel)	1	d <sub>1</sub>
<b>DIN 466-M2-NI</b>	2	Material